

Tehničke karakteristike artikla: NLPXWT433S

PX protivpanična svetiljka selfcontrol 4x1W ERT-LED 3h TT

Izlazni znak zidni / protivpanična plafonska, 30m, 1h/3h/8h, LiFePO4



Tehnički podaci

Neto dužina (mm)	340,00
Neto širina (mm)	60,00
Neto visina (mm)	170,00
Neto težina (kg)	0,80
Vrsta svetiljke (prema načinu primene)	Kombinovana svetiljka sa piktogramom i osvetljenjem evakuacionog puta anti-panik svetiljka sigurnosna rasveta
VB-CPS	Sa sopstvenom baterijom
Funkcija	Samokontrola niske temperature
Verzija	Plastične svetiljke
Dizajn	PX
Bezhalogeni	Bez halogeno plastično kućište
Opis boje	RAL 9003 (bela)

Tehnički podaci - nastavak

Piktogram	Slide-in pictogram set (2x man in the door and one arrow that can be rotated by 90°) included in accordance with ISO 7010
Područje prepoznavanja/domet (m)	30
Izvor svetla	ERT-LED (4W)
Lumen	1h: 520;3h: 520;8h: 210
Opseg napona (V)	230V AC 50Hz ±20%
Power maintained mode (W)	5,90
Power non-maintained mode (W)	0,90
Power max. (W)	7,30
Baterije (V/Ah)	2x 3,2V/3,3Ah LiFePO4-TT
IP stepen zaštite	IP65
Otpornost na udar	IK05
Način montaže	Stropna ugradna opcija Univerzalna Plafonska nadgradna Montaža na zid
Min. temperatura okoline (°C)	-15
Maks. temperatura okoline (°C)	40
AA Klasa E 8101	AA4
Proizvođač	Schrack

**Spacing table with square lens (for optimized illumination of the pictogram)
(included in scope delivery) - Minimum illuminance on the centerline at +/- 0.5
m: 1 lx - Maintenance factor 0.80 - Autonomy time 1h/3h**

					
2,00	5,03	11,47	11,47	11,47	5,03
2,50	5,75	13,22	13,22	13,22	5,75
3,00	6,35	14,79	14,79	14,79	6,35
3,50	6,59	16,2	16,2	16,2	6,59
4,00	6,69	17,48	17,48	17,48	6,69
5,00	4,78	18,72	18,72	18,72	4,78
6,00	2,9	17,57	17,57	17,57	2,9

Spacing table with corridor lens (NLLSYSF4 must be ordered separately) - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80 - Autonomy time 1h/3h

					
2,00	5,41	12,15	10,43	8,84	3,68
2,50	6,51	14,33	12,02	9,84	4
3,00	7,51	16,36	13,52	10,71	4,2
3,50	8,44	18,55	14,73	11,34	4,34
4,00	9,3	20,61	16,07	11,78	4,43
5,00	10,86	24,4	18,29	12,37	4,4
6,00	8,41	27,81	20,14	12,65	4,29
7,00	6,41	26,48	18,47	12,49	4,18
8,00	4,79	26,58	16,62	12,3	3,87
9,00	2,76	23,86	14,84	12,13	3,03

Spacing table with round lens (NLLSYSR4 must be ordered separately) - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80 - Autonomy time 1h/3h

					
2,00	4,21	9,38	9,38	9,38	4,21
2,50	5,05	10,9	10,9	10,9	5,05
3,00	5,81	12,56	12,56	12,56	5,81
3,50	6,51	14,22	14,22	14,22	6,51
4,00	7,14	15,77	15,77	15,77	7,14
5,00	7,55	18,58	18,58	18,58	7,55
6,00	4,89	19,41	19,41	19,41	4,89
7,00	3	18,4	18,4	18,4	3

Spacing table with spot lens (NLLSYSS4 must be ordered separately) - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80 - Autonomy time 1h/3h

					
2,00	1,91	4,79	4,79	4,79	1,91
2,50	2,39	5,99	5,99	5,99	2,39
3,00	2,87	7,19	7,19	7,19	2,87
3,50	3,33	8,39	8,39	8,39	3,33
4,00	3,57	8,74	8,74	8,74	3,57
5,00	4,04	9,53	9,53	9,53	4,04
6,00	4,51	10,45	10,45	10,45	4,51
7,00	4,88	11,4	11,4	11,4	4,88
8,00	5,26	12,39	12,39	12,39	5,26
9,00	5,56	13,23	13,23	13,23	5,56
10,00	5,78	13,93	13,93	13,93	5,78
12,00	6,02	15,36	15,36	15,36	6,02
14,00	5,98	16,35	16,35	16,35	5,98
16,00	5,67	16,93	16,93	16,93	5,67

**Spacing table with high corridor lens (NLLSYSH4 must be ordered separately)
- Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80 -
Autonomy time 1h/3h**

					
2,00	2,2	5,89	7,64	9,38	4,09
2,50	2,75	7,36	9,55	11,73	5,12
3,00	3,28	8,73	11,31	13,87	6,05
3,50	3,34	9,06	12,13	15,12	6,7
4,00	3,35	9,27	12,88	16,55	7,29
5,00	3,27	9,5	14,34	19,2	8,23
6,00	2,74	9,51	15,51	21,52	8,89
7,00	2,57	9,35	16,35	23,36	9,38
8,00	2,65	8,59	16,65	24,76	9,72
9,00	2,66	7,66	16,65	25,97	9,9
10,00	2,62	7,25	16,9	26,85	9,98
12,00	2,62	7,55	16,92	28,07	8,99
14,00	2,39	7,41	15,75	28,23	8,54
16,00	1,98	7,5	15,31	26,42	7,13

**Spacing table with square lens (for optimized illumination of the pictogram)
(included in scope delivery) - Minimum illuminance on the centerline at +/- 0.5
m: 1 lx - Maintenance factor 0.80 - Autonomy time 8h**

					
2,00	4,06	9,64	9,64	9,64	4,06
2,50	4,26	10,97	10,97	10,97	4,26
3,00	3,4	11,71	11,71	11,71	3,4
3,50	2,36	11,6	11,6	11,6	2,36
4,00	1,44	10,77	10,77	10,77	1,44

**Spacing table with corridor lens (NLLSYSF4 must be ordered separately) - Min.
illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80 -
Autonomy time 8h**

					
2,00	4,81	10,66	8,73	6,92	2,67
2,50	5,69	12,76	9,97	7,4	2,77
3,00	6,48	14,67	11,15	7,73	2,79
3,50	6,22	16,42	12,1	7,93	2,74
4,00	4,36	16,16	12	8,01	2,67
5,00	3,1	16,59	10,33	7,79	2,45

Spacing table with round lens (NLLSYSR4 must be ordered separately) - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80 - Autonomy time 8h

					
2,00	3,81	8,26	8,26	8,26	3,81
2,50	4,47	9,87	9,87	9,87	4,47
3,00	4,81	11,3	11,3	11,3	4,81
3,50	4,26	12,52	12,52	12,52	4,26
4,00	2,74	11,92	11,92	11,92	2,74
5,00	0,13	11,27	11,27	11,27	0,13

Spacing table with spot lens (NLLSYSS4 must be ordered separately) - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80 - Autonomy time 8h

					
2,00	1,91	4,79	4,79	4,79	1,91
2,50	2,22	5,47	5,47	5,47	2,22
3,00	2,44	5,8	5,8	5,8	2,44
3,50	2,7	6,33	6,33	6,33	2,7
4,00	2,92	6,74	6,74	6,74	2,92
5,00	3,29	7,76	7,76	7,76	3,29
6,00	3,58	8,57	8,57	8,57	3,58
7,00	3,75	9,32	9,32	9,32	3,75
8,00	3,81	9,94	9,94	9,94	3,81
9,00	3,77	10,4	10,4	10,4	3,77
10,00	3,62	10,69	10,69	10,69	3,62
12,00	2,95	10,81	10,81	10,81	2,95
14,00	1	10,34	10,34	10,34	1

Spacing table with high corridor lens (NLLSYSH4 must be ordered separately) - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80 - Autonomy time 8h

					
2,00	2,06	5,52	7,24	8,93	3,91
2,50	2,1	5,8	8,03	10,3	4,51
3,00	2,06	5,96	8,82	11,65	5
3,50	1,94	6,02	9,43	12,85	5,35
4,00	1,72	5,99	9,96	13,94	5,65
5,00	1,68	5,49	10,46	15,44	6,03
6,00	1,67	4,76	10,55	16,56	6,2
7,00	1,68	4,74	10,65	17,3	5,73
8,00	1,64	4,79	10,22	17,72	5,48
9,00	1,5	4,72	9,82	17,56	5,28
10,00	1,3	4,77	9,65	16,56	4,51

Tabela artikla

OPIS	Kat. broj
PX protivpanična svetiljka selfcontrol 4x1 W ERT-LED 3h TT	NLPXWT433S
Izlazni znak zidni / protivpanična plafonska, 30m, 1h/3h/8h, LiFePO4	
Dodatni pribor	
Poklopac za zaštitu od kiše za KC , pleksi	NLKCRD
Zaštitna rešetka za serije KC, KX, PF, LX, RX	NLBALL2
I x h x d: 450 x 280 x 125mm	
Piktogram set NLPX 2x kolica 2x dijagonalne	NLPXPIKTO2
2-delni piktogrami, vidljivost: 30m	
	NLTESTSC2
Zaštitni poklopac za test dugme NLTEST2	NLTEST2COV
39	
Accu LiFePO4 3.2V 3.3Ah za LED svetiljku	NLAKKU323T
LiFePO4 - Litijum-gvožđe fosfat baterija za niske temperature, UN3480 - UN 3480 : Litijum-jonske baterije, -25° do 40°C	